



 Laifual Drive

Technical Requirements:

1. Please use the grease specified by our company (LF-2 or F-3).
 2. The * in the drawing is the installation reference size, please follow the installation size requirements.
 3. For details of size, please confirm with the delivery specification drawings.

LSD-20-XX-U-I				Model	Reduction ratio	Rated torque at 2000r/min input		Permissible peak torque at start and stop		Permissible maximum value for average load		Permissible maximum momentary torque		Permissible maximum input rotational speed (Grease)	Permissible average input rotational speed (Grease)	Backlash	weight	Desian life	
MODEL	U	T	W																
Wave generator-A φ8	φ8H7	9.4 ^{+0.1} _{-0.1}	3P9/JS9			Nm	kgfm	Nm	kgfm	Nm	kgfm	Nm	kgfm	r/min	r/min	Arc Sec	Kg	Hour	
Wave generator-A φ20	φ20H7	/		20	50	17	1.7	39	4	24	2.4	69	7	6500	3500	≤20	LSD-I:0.68	9000	
		/			80	21	2.1	46	4.7	30	3.1	81	0.8					10000	
		/			100	28	2.9	57	5.8	34	3.5	95	9.7					10000	