



 *Laifual Drive*

Technical Requirements:

1. Please use the grease specified by our company (LF-2 or F-3).
 2. The * in the drawing is the installation reference size, please follow the installation size requirements.
 3. For details of size, please confirm with the delivery specification drawings.

LSD-20-P-XX-U-I

LSD-20-P-XX-U-I				Model	Reduction ratio	Rated torque at 2000r/min input		Permissible peak torque at start and stop		Permissible maximum value for average load		Permissible maximum momentary torque		Permissible maximum input rotational speed (Grease)	Permissible average input rotational speed (Grease)	Backlash	weight	Desian life
MODEL	U	T	W			Nm	kgfm	Nm	kgfm	Nm	kgfm	Nm	kgfm	r/min	r/min	Arc Sec	Kg	Hour
Wave generator-A φ8	φ8H7	9.4 ^{+0.1} ₀	3P9/JS9	20	50	17	1.7	39	4	24	2.4	69	7	6500	3500	≤20	LSD-P:0.96	9000
Wave generator-A φ20	φ20H7				80	21	2.1	46	4.7	30	3.1	81	0.8					10000
					100	28	2.9	57	5.8	34	3.5	95	9.7					10000